

# Eaton 10250T15112

Catalog Number: 10250T15112

Eaton 10250T, Selector switch, 30.5 mm, Heavy-Duty, Cam 1, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Two-position, Key, Left only

## General specifications



### Product Name

Eaton 10250T pushbutton

### Catalog Number

10250T15112

### UPC

782113227481

### Product Length/Depth

1.9 in

### Product Height

2.2 in

### Product Width

2 in

### Product Weight

0.35 lb

### Warranty

1 year

### Compliances

CE Marked

### Certifications

UL Listed

CSA Certified



Powering Business Worldwide

## defaultTaxonomyAttributeLabel

### Type

30.5 mm, Heavy-Duty

### Cam code

Cam 1

### Key removal position

Left only

### Product Category

Selector switch

### Actuator

Key operated

### Throw type

60 °

### Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

### Illumination

Non-illuminated

### Number of positions

2

### Series

10250T

## Resources

### Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

### Multimedia

[How to size and select a Power Supply](#)

### Specifications and datasheets

[Eaton Specification Sheet - 10250T15112](#)

[Cam selection for pushbutton selectors](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)