



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



53AHALMSSSW4 *Delisted* 53W A19 Halogen Lamp

Sylvania-Ledvance

Catalog Number	53AHALMSSSW4
Manufacturer	Sylvania-Ledvance
Description	OBS50018 Tungsten Halogen A19 Lamp 53 Watt 120 Volt Medium Base Modified Spectrum Super Soft White Finish
Weight per unit	0.1200 (lbs/each)
Product Category	Line BT, TB Shape Lamps

Features

average life	1000
Base	Medium Aluminum
dimnable	Yes
lumens	1050
Shape	A17
start type	Instant
Voltage Rating	120
Wattage	53

Material, Color, and Finish

color rendering index (cri)	100
color temperature	2950
Finish	Soft White

Descriptions

Description	*DELISTED* 53W A19 HALOGEN LAMP
extra long description	SYL 53AHALMSSSW4-120V/50018 53AHALM
Long Description	OBS50018 Tungsten Halogen A19 Lamp 53 Watt 120 Volt Medium Base Modified Spectrum Super Soft White Finish
Product Type	53AHALMSSSW4120V 48/CS 4/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135500183
Manufacturers Part Number	53AHALMSSSW4-120V/50018
UPC	046135500183

Taxonomies, Classifications, and Categories

Category Description	QUARTZ
Type	TUNGSTEN HALOGEN

Packaging

Carton	48
Package	12
Weight Per each	0.12



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application Medium Screwbase or bi-pin