

Eaton CHQ225

Catalog Number: CHQ225

3/4" Thermal magnetic circuit breakers, Type CHQ 3/4-Inch classified replacement breaker clamshell pack, 25 A, 10 kAIC, Two-pole, 120/240V, CHQ, Common breaker trip, (1) #14-8 AWG, (2) #14-10 AWG Cu/Al, Q30, CHQ, Type CH Loadcenters



General specifications

Product Name	Catalog Number
Eaton Classified 3/4" thermal magnetic circuit breaker	CHQ225
	UPC
	782113010915

Product Length/Depth	Product Height
2.5 in	3 in

Product Width	Product Weight
1.5 in	0.6 lb

Warranty	Certifications
Limited lifetime residential, 1 year commercial	UL 489

Catalog Notes
Replacement for Square D Type QO Breakers. Requires two 3/4-inch (19.1 mm) spaces.

defaultTaxonomyAttributeLabel

Type

Type CHQ 3/4-Inch classified replacement breaker clamshell pack

Special features

Clamshell pack

Amperage Rating

25 A

Voltage rating

120/240 V

Trip Type

Common breaker trip

Circuit breaker type

CH

Used with

Type CH Loadcenters

Interrupt rating

10 kAIC

Main circuit breaker

CHQ

Wire size

(2) #14-10 AWG Cu/Al

(1) #14-8 AWG

Number of poles

Two-pole

Quantity

30

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

[Standard circuit breaker catalog numbers - 5651B63SH09](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CHQ225](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)