

# Eaton E50KL142

Catalog Number: E50KL142

Limit Switch Operator, E50, Accessory, Loop, Used with side rotary, Nylatron

## General specifications



**Product Name** **Catalog Number**

Eaton E50 NEMA heavy duty plug-in limit E50KL142  
switch operator

**UPC**

782113307749

**Product Length/Depth**

1.9 in

**Product Height**

5.5 in

**Product Width**

0.74 in

**Product Weight**

0.3 lb

**Warranty**

1 year

**Compliances**

RoHS Compliant

**Certifications**

UL Listed

CSA Certified

CE



Powering Business Worldwide

Type

Accessory

Used with

Used with side rotary

Series

E50

Switch type

Loop

Operating temperature - max

200 °F

Operating temperature - min

10 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,  
NEMA 6P, NEMA 13, IP67

Material

Nylatron

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E50KL142](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)