



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LT3 3" Met L/T, Non UL 25' *Southwire Company*

|                  |                                                                                                                                                                                                                                                                               |
|------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | LT3                                                                                                                                                                                                                                                                           |
| Manufacturer     | Southwire Company                                                                                                                                                                                                                                                             |
| Description      | Liquidtight Flexible Conduit, 3 In Trade Size, 3.46 to 3.5 In Conduit Outer Diameter, 3.07 to 3.1 In Conduit Inner Diameter, Titan(R) Ef Style, 25 FT Length, Galvanized, Gray, 18 In Bend Radius, +14 °F Operating Temperature, +140 °F Operating Temperature, 209 LB/100 FT |
| Weight per unit  | 1.5 (lbs/ft)                                                                                                                                                                                                                                                                  |
| Product Category | Liquid Tight Conduit                                                                                                                                                                                                                                                          |

### Features

|                  |      |
|------------------|------|
| outside diameter | 3415 |
|------------------|------|

### Dimensions and Weight

|          |    |
|----------|----|
| Diameter | 3" |
|----------|----|

### Descriptions

|                        |                                     |
|------------------------|-------------------------------------|
| Description            | 3" MET L/T, NON UL 25'              |
| extra long description | SWC 55107401 Titan2 Type EF Extra-F |

### Manufacturer Information

|      |                |
|------|----------------|
| GTIN | 00032886043130 |
| UPC  | 032886043130   |

### Taxonomies, Classifications, and Categories

|                      |              |
|----------------------|--------------|
| Category Description | Liquid Tight |
|----------------------|--------------|

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 25   |
| Weight Per foot | 1.45 |