

Eaton BAB1020

Catalog Number: BAB1020

Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,Bolt-on mounting, High intensity discharge,20 A,10 kAIC,Single-pole,120/240 V,Non-Interchangeable,Q7,BAB



General specifications

Product Name	Catalog Number
Eaton BAB thermal magnetic circuit breaker	BAB1020
	UPC
	786679301203
Product Length/Depth	Product Height
3 in	2.5 in
Product Width	Product Weight
1 in	0.2 lb
Warranty	Certifications
1 year	UL Listed
	CSA Certified
Catalog Notes	
HACR rated	

Physical Attributes

Circuit breaker type

BAB

Number of poles

Single-pole

Type

Quicklag industrial thermal-magnetic circuit breaker

Performance Ratings

Amperage Rating

20 A

Interrupt rating

10 kAIC

Trip Type

Non-Interchangeable

Voltage rating

120/240 V

Miscellaneous

Quantity

7

Special features

Bolt-on mounting

High intensity discharge

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

Multimedia

[Circuit Breakers Explained](#)

Specifications and datasheets

[Eaton Specification Sheet - BAB1020](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)