

# Eaton CL115

Catalog Number: CL115

Eaton Classified 3/4" thermal magnetic circuit breaker, Type CL 1-Inch classified replacement breaker, 15 A, 10 kAIC, Single-pole, 120/240V, CL, #14-4 AWG Cu/Al, CL

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Classified 3/4" thermal magnetic circuit breaker	CL115
	UPC
	786676011549

<b>Product Length/Depth</b>	<b>Product Height</b>
3 in	3 in

<b>Product Width</b>	<b>Product Weight</b>
1 in	0.3 lb

<b>Warranty</b>	<b>Certifications</b>
Limited lifetime residential, 1 year commercial	UL 489

**Catalog Notes**  
Replacement for Square D Homeline, GE Type THQ, Crouse-Hinds Type MP, Thomas and Betts Type TB, Murray Type MP, ITE/Siemens Type QP. Requires 1-inch (25.4 mm) space.



**Type**

Type CL 1-Inch classified replacement breaker

**Amperage Rating**

15 A

**Voltage rating**

120/240 V

**Circuit breaker type**

CH

**Used with**

Square D HOMELINE, General Electric, Crouse-Hinds, Thomas and Betts, Murray and ITE/Siemens Load centers

**Interrupt rating**

10 kAIC

**Main circuit breaker**

CL

**Wire size**

#14-4 AWG Cu/Al

**Number of poles**

Single-pole

**Brochures**

[Loadcenters and Circuit Breakers](#)

[Standard circuit breaker catalog numbers - 5651B63SH09](#)

**Catalogs**

[Eaton's Volume 1—Residential and Light Commercial](#)

**Specifications and datasheets**

[Eaton Specification Sheet - CL115](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)