

Eaton FRS-R-30

Catalog Number: FRS-R-30

Eaton Bussmann series FRS-R fuse, 30 A, Dual, Class RK5, Non-indicating, Ferrule end x ferrule end, 10 sec at 500%, 20 kAIC at 300 Vdc|200 kAIC at 600 V, Standard, 600 V, 300 Vdc



General specifications

Product Name	Catalog Number
Eaton Bussmann series FRS-R fuse	FRS-R-30
UPC	Product Length/Depth
051712508346	11.63 in
Product Height	Product Width
2.34 in	2.34 in
Product Weight	Warranty
2.25 lb	Not Applicable
Compliances	
CE Marked	

Electrical rating

Amperage Rating

30 A

Interrupt rating

20 kAIC at 300 Vdc

200 kAIC at 600 Vac

Response time

10 sec at 500%

Voltage rating

600 Vac, 300 Vdc

Physical details

Number of elements

Dual

Packaging type

Standard

General information

Class

Class RK5

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Resources

Catalogs

[Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses](#)

[Bussmann series complete full line catalog no. 1007](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - FRS-R-30](#)

Technical data sheets

[FRS-R-30-FUSETRON DUAL ELEMENT FUSE CLASS RK5](#)

Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)