



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S29835 9.8WATT A19 Led 27K

Satco

Catalog Number	S29835
Manufacturer	Satco
Description	A19 Led Lamp, 220 ° Beam Angle, 2700 K, 800 LM Brightness (Lumens), 9.8 W, 120 V, Frosted White, 25000 H Average Life, Medium Base, Dimmable, 2.38 In Diameter, 4.17 In Length, 0.98 Power Factor, -4 °F Operating Temperature, +113 °F Operating Temperature, 0.15 LB
Weight per unit	0.1900 (lbs/each)
Product Category	Led A-Line A Shape Lamps

Features

connection	Medium
Fixture Type	Type A
lumens	800
Material	Metal;Plastic
Shape	A19
Voltage Rating	120
Warranty	5 Year Limited - 10 hr per day

Material, Color, and Finish

Color	Frosted White
-------	---------------

Dimensions and Weight

Size	MOL: 4.19, MOD: 2.38
------	----------------------

Descriptions

Description	9.8WATT A19 LED 27K
extra long description	SATCO S29835 9.8A19/OMNI/220/LED/27
Special Features	Dimmable: Yes Dimmable;Operating Temp: -20C (-4F) to a maximum of +45C (+113F);Power Factor: 0.98;Safety Listing: cULus - Damp;SDS Class: LED_Lamp;Tested Lumens: 800

Manufacturer Information

GTIN	00045923298356
UPC	045923298356

Taxonomies, Classifications, and Categories

Category Description	LED A-LINE SHAPE LAMPS
Type	Lamps

Packaging

Carton	1
Package	6
Weight Per each	0.19



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)
standard	cULus - Damp