



## FITTINGS APPROVED FOR USE WITH ALUMINUM EMT

| FITTING STYLE    | UL File E24001                                               |
|------------------|--------------------------------------------------------------|
| SETSCREW TYPE    | 230-DC2, -DCI2 thru 234-DC2, -DCI2                           |
|                  | 235-DC, -DC2, -DCI, -DC2I                                    |
|                  | 236-DC, -DCI thru 239-DC, -DCI                               |
|                  | 234-SBLK, -SR, -SO, -SY, -SG, -SBLU, -SW                     |
|                  |                                                              |
|                  | 244-SBLK, -SR, -SO, -SY, -SG, -SBLU, -SW                     |
|                  | 240-DC thru 249-DC                                           |
| COMPRESSION TYPE |                                                              |
|                  | 250-DC2, -RT2, -DCI2, -RTI2 thru 254-DC2, -RT2, -DCI2, -RTI2 |
|                  | 255-DC2, -DCI2 thru 259-DC2, -DCI2                           |
|                  |                                                              |
|                  | 260-DC2, -RT2, -DCI2, -RTI2 thru 264-DC2, -RT2, -DCI2, -RTI2 |
|                  | 265-DC thru 269-DC                                           |
| PUSH-EMT® TYPE   | 250-MSRT, 251-MSRT                                           |
|                  | 260-MSRT, 261-MSRT                                           |



## FITTINGS APPROVED FOR USE WITH ALUMINUM EMT

| FITTING STYLE           | UL File E24001                                               |
|-------------------------|--------------------------------------------------------------|
| <b>SETSCREW TYPE</b>    | 230-DC2, -DCI2 thru 234-DC2, -DCI2                           |
|                         | 235-DC, -DC2, -DCI, -DCI2                                    |
|                         | 236-DC, -DCI thru 239-DC, -DCI                               |
|                         | 234-SBLK, -SR, -SO, -SY, -SG, -SBLU, -SW                     |
|                         |                                                              |
|                         | 244-SBLK, -SR, -SO, -SY, -SG, -SBLU, -SW                     |
|                         | 240-DC thru 249-DC                                           |
| <b>COMPRESSION TYPE</b> |                                                              |
|                         | 250-DC2, -RT2, -DCI2, -RTI2 thru 254-DC2, -RT2, -DCI2, -RTI2 |
|                         | 255-DC2, -DCI2 thru 259-DC2, -DCI2                           |
|                         |                                                              |
|                         | 260-DC2, -RT2, -DCI2, -RTI2 thru 264-DC2, -RT2, -DCI2, -RTI2 |
|                         | 265-DC thru 269-DC                                           |
| <b>PUSH-EMT® TYPE</b>   |                                                              |
|                         | 250-MSRT, 251-MSRT<br>260-MSRT, 261-MSRT                     |