



CAT6 EZ-RJ45 CONNECTORS, PACK OF 25

AC346025 | [On-Q](#)

FEATURES & BENEFITS

Our Cat 6 EZ-RJ45 Connector makes it easy to quickly and efficiently terminate wires of any length. Large cable openings reduce the distance between the wires and contacts, creating optimal performance and reliable connections every time. Available in packs of 25.



SPECIFICATIONS

GENERAL INFO

Cable Type: For solid or stranded conductors
Category Performance Application: Cat6+
Color: Clear
Number Of Ports: 1
Pair Count: 4
Performance Category: Cat6
Quantity: sold in Packs of 25
Termination: Insulation displacement
Typical Applications: Bulk wire termination for data applications

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

DIMENSIONS

Cable Diameter Range: Conductors with an O.D. Range of 0.037" to 0.042"
Depth (US): 0.885
Height (US): 0.312
Width (US): 0.46
Product Weight (US): 0.004 Lbs

TECHNICAL INFORMATION

Humidity: Max 93% non-condensing

Material: High impact polycarbonate

OhmValue: Contact Resistance 10 milliohms max

Operating Temperature (Celsius): minus 40 to +85

Product Fits Into: RJ45 Jacks



CAT6 EZ-RJ45 CONNECTORS, PACK OF 25

AC346025 | [On-Q](#)

FEATURES & BENEFITS

Our Cat 6 EZ-RJ45 Connector makes it easy to quickly and efficiently terminate wires of any length. Large cable openings reduce the distance between the wires and contacts, creating optimal performance and reliable connections every time. Available in packs of 25.



SPECIFICATIONS

GENERAL INFO

Cable Type: For solid or stranded conductors
Category Performance Application: Cat6+
Color: Clear
Number Of Ports: 1
Pair Count: 4
Performance Category: Cat6
Quantity: sold in Packs of 25
Termination: Insulation displacement
Typical Applications: Bulk wire termination for data applications

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

DIMENSIONS

Cable Diameter Range: Conductors with an O.D. Range of 0.037" to 0.042"
Depth (US): 0.885
Height (US): 0.312
Width (US): 0.46
Product Weight (US): 0.004 Lbs

TECHNICAL INFORMATION

Humidity: Max 93% non-condensing

Material: High impact polycarbonate

OhmValue: Contact Resistance 10 milliohms max

Operating Temperature (Celsius): minus 40 to +85

Product Fits Into: RJ45 Jacks