

Eaton CL130

Catalog Number: CL130

Eaton Classified 3/4" thermal magnetic circuit breaker, Type CL 1-Inch classified replacement breaker, 30 A, 10 kAIC, Single-pole, 120/240V, CL, #14-4 AWG Cu/Al, CL, Type CH Loadcenters

General specifications



Product Name

Eaton Classified 3/4" thermal magnetic circuit breaker

Catalog Number

CL130

UPC

786676011570

Product Length/Depth

0.9 in

Product Height

2.5 in

Product Width

3.1 in

Product Weight

0.25 lb

Warranty

Limited lifetime residential, 1 year commercial

Certifications

UL 489

Catalog Notes

Replacement for Square D Homeline, GE Type THQ, Crouse-Hinds Type MP, Thomas and Betts Type TB, Murray Type MP, ITE/Siemens Type QP. Requires 1-inch (25.4 mm) space.

Type

Type CL 1-Inch classified replacement breaker

Amperage Rating

30 A

Voltage rating

120/240 V

Circuit breaker type

CH

Used with

Type CH Loadcenters

Interrupt rating

10 kAIC

Main circuit breaker

CL

Wire size

#14-4 AWG Cu/Al

Number of poles

Single-pole

Brochures

[Loadcenters and Circuit Breakers](#)

[Standard circuit breaker catalog numbers - 5651B63SH09](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CL130](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)