



SKU: GSW-13

UPC: 0032076890131

Features & Benefits:

Description: SPDT Toggle Switch

Specs

Dimensions

Lead Length	None
-------------	------

Additional Class Attributes

Control Style	2-Pole
Illuminated	No
Mounting Method	Recessed
Number of Positions	3
Speeds	2
Switch Outlet Grade	Commercial
Switch Style	Standard
Switch Type	Toggle
Warranty	1 Year
Wattage	5540

Material and Finish

Material	Nickel
----------	--------

Additional Technical Specifications

Connector Amperage Rating CU (Derated where applicable)	20 Amps
Contact Arrangement	SPST
Contact Type	Maintained
Terminal Type	Screw

Testing Standards

Prop65 Compliance	WARNING: Cancer and Reproductive Harm - www.P65warnings.ca.gov
-------------------	--

Color

Color

Chrome

Voltage

Maximum Voltage

277 V

Minimum Voltage

125 V

Environment and Temperature

Environmental Conditions

Indoor

General

Bag Quantity

1

Carton Quantity Description

STD PACK QTY 5

UPC Code

03207689013