

# Eaton S20N11P01P

Catalog Number: S20N11P01P

Eaton General purpose encapsulated transformer, EP, copper, NEMA 3R, 67P, 60 Hz, 180C, 1 kVA, 1 kVA, wall, single-phase, 240 V, 480 V, 120/240 V, NEMA ST-20, NONE, 115 °C rise, 1 KVA, indoor-outdoor, 3A

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton General purpose encapsulated transformer	S20N11P01P
	<b>UPC</b>
	786680073687
<b>Product Length/Depth</b>	<b>Product Height</b>
6.56 in	13.03 in
<b>Product Width</b>	<b>Product Weight</b>
5.53 in	25 lb
<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

## Physical Attributes

### Coil material

Copper

### Design

EP

### Enclosure

NEMA 3R

### Frame

67P

### Insulation

180 °C

### Mounting

Wall

### Tap size

None

### Type

General-Purpose Encapsulated Transformer

### Wiring connection

3A

## Miscellaneous

### Weathershield

Indoor-Outdoor

## Performance Ratings

### Frequency rating

60 Hz

### Kva Rating

1 kVA

### kVA

1 kVA

### Phase

Single-phase

### Primary voltage

240 V, 480 V

### Secondary Voltage

120/240 V

### Sound Level

NEMA ST-20

### Temperature rise

115 °C rise

### Volt ampere rating

1 kVA

## Resources

### Catalogs

Eaton's Volume 2—Commercial Distribution

### Specifications and datasheets

Eaton Specification Sheet - S20N11P01P



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)