

# Eaton S20N11S10N

Catalog Number: S20N11S10N

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 179, 60 Hz, single-phase, 240 V, 480 V, 120/240 V, NONE, 115 °C rise, 10 KVA, indoor-outdoor, 3A



## General specifications

|  |                       |
|--|-----------------------|
| <b>Product Name</b>  | <b>Catalog Number</b> |
| Eaton General purpose encapsulated transformer   | S20N11S10N            |
|  | <b>UPC</b>            |
|  | 786680102998          |
| <b>Product Length/Depth</b>  | <b>Product Height</b> |
| 10.52 in   | 19 in                 |
| <b>Product Width</b>   | <b>Product Weight</b> |
| 13.38 in   | 189 lb                |
| <b>Warranty</b>  | <b>Certifications</b> |
| Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |                       |
|  | <b>Catalog Notes</b>  |
|  | Model N               |

## Physical Attributes

### Coil material

Aluminum

### Design

EP

### Enclosure

NEMA 3R

### Frame

179

### Tap size

None

### Type

General-Purpose Encapsulated Transformer

### Wiring connection

3A

## Performance Ratings

### Frequency rating

60 Hz

### Phase

Single-phase

### Primary voltage

240 V, 480 V

### Secondary Voltage

120/240 V

### Temperature rise

115 °C rise

### Volt ampere rating

10 kVA

## Miscellaneous

### Weathershield

Indoor-Outdoor

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - S20N11S10N](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)