



# S8122

F54T5/850/HO/ENV  
54 watt; T5; Fluorescent; 5000K Natural Light; 85 CRI;  
Miniature Bi Pin base

## Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards



S8122

| Item Number   | UPC            | Watts          | Lamp Shape  | Base                | ANSI Base      | Lamp Code        | MOD In Inches |
|---------------|----------------|----------------|-------------|---------------------|----------------|------------------|---------------|
| S8122         | 045923081224   | 54             | T5          | Miniature Bi Pin    | G5             | F54T5/850/HO/ENV | 0.63"         |
| MOL In Inches | Nominal Length | Initial Lumens | Mean Lumens | Average Rated Hours | Kelvin Temp    | Color            | Pack          |
| 45.8"         | 48"            | 5000           | 4650        | 24000               | 5000           | Natural Light    | 40            |
| Package Type  |                |                | CRI         |                     | RoHS Compliant |                  |               |
| Sleeve        |                |                | 85          |                     | Yes            |                  |               |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S8122

F54T5/850/HO/ENV  
54 watt; T5; Fluorescent; 5000K Natural Light; 85 CRI;  
Miniature Bi Pin base

## Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards



S8122

| Item Number   | UPC            | Watts          | Lamp Shape  | Base                | ANSI Base      | Lamp Code        | MOD In Inches |
|---------------|----------------|----------------|-------------|---------------------|----------------|------------------|---------------|
| S8122         | 045923081224   | 54             | T5          | Miniature Bi Pin    | G5             | F54T5/850/HO/ENV | 0.63"         |
| MOL In Inches | Nominal Length | Initial Lumens | Mean Lumens | Average Rated Hours | Kelvin Temp    | Color            | Pack          |
| 45.8"         | 48"            | 5000           | 4650        | 24000               | 5000           | Natural Light    | 40            |
| Package Type  |                |                | CRI         |                     | RoHS Compliant |                  |               |
| Sleeve        |                |                | 85          |                     | Yes            |                  |               |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

