



Product Quick Search



[HOME](#) | [WHERE TO BUY](#) | [CONTACT US](#) | [SITE MAP](#)

- [PRODUCTS](#)
- [SUPPORT](#)
- [NEWS/EVENTS](#)
- [ABOUT BALDOR](#)
- [INVESTOR RELATIONS](#)

**General Information**

- [Overview](#)
- [Specifications](#)
- [Performance Data](#)
- [Parts List](#)
- [Dimensional Dwg](#)
- [Connection Diag](#)
- [Product Literature](#)
- [More Information](#)**
- [Locate Distributor](#)
- [Baldor Sales Offices](#)

**[Return to List](#)**

[AC Motors](#) | [General Purpose](#) |

## Specifications: L3510

Catalog Number:	L3510
Specification Number:	35J383X945
Horsepower:	1
Voltage:	115/230
Hertz:	60
Phase:	1
Full Load Amps:	12.8/6.4
Usable at 208 Volts:	7
RPM:	1725
Frame Size:	56/56H
Service Factor:	1.15
Rating:	40C AMB-CONT
Locked Rotor Code:	K
NEMA Design Code:	L
Insulation Class:	B
Full Load Efficiency:	67
Power Factor:	73
Enclosure:	TEFC
Baldor Type:	3524L
DE Bearing:	6205
ODE Bearing:	6203
Electrical Specification Number:	35WGX945
Mechanical Specification Number:	35J383
Base:	RG
Mounting:	F1

\* For certified information, contact your local [Baldor office](#).

[Products](#) | [Support](#) | [News/Events](#) | [About Baldor](#) | [Investor Relations](#) | [Home](#)