



Product Quick Search



[HOME](#) | [WHERE TO BUY](#) | [CONTACT US](#) | [SITE MAP](#)

- PRODUCTS
- SUPPORT
- NEWS/EVENTS
- ABOUT BALDOR
- INVESTOR RELATIONS

General Information

- [Overview](#)
- [Specifications](#)
- [Performance Data](#)
- [Parts List](#)
- [Dimensional Dwg](#)
- [Connection Diag](#)
- [Product Literature](#)
- [More Information](#)**
- [Locate Distributor](#)
- [Baldor Sales Offices](#)

[Return to List](#)

[AC Motors](#) | [Explosion Proof](#) |

Specifications: M7044T

Catalog Number:	M7044T
Specification Number:	36E145X864H1
Horsepower:	5//3
Voltage:	230/460//190/380
Hertz:	60//50
Phase:	3
Full Load Amps:	13.4/6.7//10.6/5.3
Usable at 208 Volts:	14
RPM:	1750//1460
Frame Size:	184T
Service Factor:	1.00
Rating:	40C AMB-CONT
Locked Rotor Code:	K
NEMA Design Code:	B
Insulation Class:	B
Full Load Efficiency:	87.5
Power Factor:	80
Enclosure:	N/A
Baldor Type:	3638M
DE Bearing:	N/A
ODE Bearing:	N/A
Electrical Specification Number:	36WGX864
Mechanical Specification Number:	36E145
Base:	RG
Mounting:	F1

* For certified information, contact your local [Baldor office](#).