

# Technical Specifications Wall Plate Specifications

Pass & Seymour



## Application

Pass & Seymour/Legrand's broad line of Standard Size Plastic and Metal Wall Plates features the most complete range of types, sizes, colors, and finishes available. Choose from more than 1,900 standard plates in non-combustible thermoset plastic material, self-extinguishing nylon material, screwless polycarbonate material, or attractively finished metal, for residential, commercial, institutional, and industrial applications. All plastic wall plates color match to Pass & Seymour/Legrand devices.

## 3rd Party Compliance

UL Listed, Standard UL514, Cover Plates for Flush-Mounted Wiring Devices.  
CSA Certified.

## Thermoset Plastic Wall Plates Features

- Molded of non-combustible mar-proof material.
- Available in "SP" series in Standard, Junior-Jumbo, and Jumbo sizes.
- Seven standard colors available – Ivory, White, Brown, Gray, Black, Red, and Light Almond.
- Individually wrapped with color-matching screws.
- Resistant to discoloration, grease, oil, solvent and moisture.
- Nominal thickness, .070"

## Materials

Wall Plate Material	Urea
Mounting Screws	Metal, oval heads painted to match plate color



Thermoset Smooth

## TradeMaster® Thermoplastic Wall Plates Features

- Molded of rugged, practically indestructible self-extinguishing nylon. ("TP" series only.)
- Available in "TP" series, extra 3/16" width and height than Standard size plates; and "TPJ" series, extra 3/16" width and height than Junior-Jumbo size plates.
- Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.
- Preferred for hospital, industrial, institutional, and other high-abuse applications.
- Nominal thickness, .070"

## Performance

### Mechanical

Mechanical Strength	Exceeds UL514 Bend Test
Deformation	Exceeds UL514 Corner Peel

### Environmental

Chemical-Resistant	
Flammability	UL94 V2

## Materials

Wall Plate Material	.070" Nylon 6
Wall Plate Finish	Matte
Mounting Screws	Steel, oval heads painted to match plate color



TP Nylon Smooth

## Screwless Polycarbonate Wall Plates Features

- Molded of .065" thick polycarbonate with matte finish.
- Subplate made of .042" zinc-plated steel.
- Available in "SW" series, extra 1/8" width and height than Standard size plates.
- Available in Ivory, White, Gray, Black, and Light Almond.
- Oversized opening to accommodate all NEMA 26 decorator-style openings.

## Performance

Flammability	UL94 V2
--------------	---------

## Materials

Wall Plate Material	.065" Polycarbonate
Wall Plate Finish	Matte
Subplate Material	.042" Zinc-plated steel



Screwless Polycarbonate