



SNA Terminal Blocks

T&B Catalog Number:

011511607

UPC Number:

66201995587

Status:

Active

Description:

Gray, feed through terminal block with 6 mm spacing, 30 Amp rated UL current with screw clamp connection that accepts 22-10 AWG UL wire range

Features

Self-locking clamp design prevents screw loosening

Funneled side entry for up to two ferruled or non-ferruled solid or stranded wires

Touch-safe IP20 protection

High quality steel offers a very high over-torque resistance

Compensates for the flattening of copper under contact pressure

Clamp is protected from harsh environments by a zinc bichromate surface treatment

Application

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

General

Style	Feed Through
Color	Gray
Mounting	DIN 1-3
Series	M 4/6
Connection Technology	Screw Clamp
UL Wire Range (AWG)	22-10
Rated IEC Wire Range (Solid) (mm ²)	4
Rated CSA Wire Size (AWG)	10

Dimension Information

L x W x H (mm)	44.5 x 6 x 53
Spacing (mm)	6
L x W x H (in)	1.75 x 0.238 x 2.18
Spacing (inches)	0.236

Specifications

UL Current (Amps)	30
UL Voltage (VAC)	600
Rated UL Wire Size (AWG)	10
IEC Voltage (VAC)	800
IEC Current (Amps)	32
CSA Voltage (VAC)	600
CSA Current (Amps)	25

Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	2000

T&B Sold in UOM	Each
T&B Weight Per UOM	0.03 lbs. Each

Certifications

Approvals	UL, IEC, CSA
-----------	--------------

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com



SNA Terminal Blocks

T&B Catalog Number:

011511607

UPC Number:

66201995587

Status:

Active

Description:

Gray, feed through terminal block with 6 mm spacing, 30 Amp rated UL current with screw clamp connection that accepts 22-10 AWG UL wire range

Features

Self-locking clamp design prevents screw loosening

Funneled side entry for up to two ferruled or non-ferruled solid or stranded wires

Touch-safe IP20 protection

High quality steel offers a very high over-torque resistance

Compensates for the flattening of copper under contact pressure

Clamp is protected from harsh environments by a zinc bichromate surface treatment

Application

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

General

Style	Feed Through
Color	Gray
Mounting	DIN 1-3
Series	M 4/6
Connection Technology	Screw Clamp
UL Wire Range (AWG)	22-10
Rated IEC Wire Range (Solid) (mm ²)	4
Rated CSA Wire Size (AWG)	10

Dimension Information

L x W x H (mm)	44.5 x 6 x 53
Spacing (mm)	6
L x W x H (in)	1.75 x 0.238 x 2.18
Spacing (inches)	0.236

Specifications

UL Current (Amps)	30
UL Voltage (VAC)	600
Rated UL Wire Size (AWG)	10
IEC Voltage (VAC)	800
IEC Current (Amps)	32
CSA Voltage (VAC)	600
CSA Current (Amps)	25

Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	2000

T&B Sold in UOM	Each
T&B Weight Per UOM	0.03 lbs. Each

Certifications

Approvals	UL, IEC, CSA
-----------	--------------

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com