

Eaton 1084-4XSS6CHC

Catalog Number: 1084-4XSS6CHC

Eaton B-Line series JIC panel enclosure, 10" height, 4" length, 8" width, NEMA 4X, Hinged cover, 4XSS6CHC enclosure, Wall mount, Small single door, External mounting feet, 316 stainless steel, Seamless poured in-place gasket

General specifications



Photo is representative

Product Name	Catalog Number
Eaton B-Line series JIC panel enclosure	1084-4XSS6CHC
UPC	Product Length/Depth
782051094800	4 in
Product Height	Product Width
10 in	8 in
Product Weight	Certifications
6.7 lb	UL 50
	CSA C22.2.
	NEMA

Material/finish

Material

316 stainless steel

Wall thickness

16 gauge

Finish color

#4 brushed

Color

Gray

Model

Style

Small single door

Model

4XSS6CHC enclosure

Cover type

Hinged

Mounting method

Wall

Mounting hole details

External mounting feet

Closure type

Hinged

Special features

Cont. piano hinge, panel mount prov., s.s. doorclamps

Standards

NEMA Rating

4X

Country of origin

US

Resources

Catalogs

[Electrical Enclosure Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - 1084-4XSS6CHC](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)