Eaton 12124 RTSC

Catalog Number: 12124 RTSC

Eaton B-Line series Type 3/3R junction boxes, 12" height, 4" length, 12" width, NEMA 3R, Screw cover, RTSC enclosure, Surface mounted, Small single door, 5 bottom knockouts, Embossed thru holes, Carbon steel

General specifications

Product Name

Catalog Number

Eaton B-Line series Type 3/3R junction

12124 RTSC

boxes

UPC

782051343809

Product Length/Depth

Product Height

4 iı

12 in

Product Width

Product Weight

12 in

8.5 lb

Certifications

UL 50

CSA C22.2.

NEMA



Material/finish

Material

Carbon steel

Wall thickness

16 gauge

Finish color

Painted

Color

ANSI 61 gray

Model

Style

Small single door

Model

RTSC enclosure

Cover type

Screw

Mounting method

Surface

Mounting hole details

Embossed thru holes

Closure type

Flanged cover

Special features

Rain hood, plated screws

Bottom knockouts

5

Standards

NEMA Rating

3R

Country of origin

US

Resources

Catalogs

Type1-3-3r-enclosure-catalog-section

Specifications and datasheets

Eaton Specification Sheet - 12124 RTSC



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.

