


Phone 800-521-7326

Fax 770-745-1333

## Fender Washer 316 Stainless Steel



Ресо		Inside Diameter	Outside Diameter	Minimum	Maximum	
Catalog#	Bolt Size	+/-0.010	+/-0.010	Thickness	Thickness	Appoximate Quantity in 50 Lbs.
14X1FW316SS	1/4	9/32	1	0.0510	0.0800	3750
14X114FW316SS	1/4	9/32	1-1/4	0.0510	0.0800	2300
14X112FW316SS	1/4	9/32	1-1/2	0.0510	0.0800	1550
14X2FW316SS	1/4	9/32	2	0.0510	0.0800	810
38X114FW316SS	3/8	13/32	1-1/4	0.0510	0.0800	2350
38X112FW316SS	3/8	13/32	1-1/2	0.0510	0.0800	1650
38X2FW316SS	3/8	13/32	2	0.0510	0.0800	1000
12X112FW316SS	1/2	17/32	1-1/2	0.0510	0.0800	2000
12X2FW316SS	1/2	17/32	2	0.0510	0.0800	950

Peco Fasteners specification sheets are a reference guide to help in the selection of fasteners. Peco has made every effort to ensure the accuracy of the information. However, Peco Fasteners is not responsible for any errors that may be contained within these sheets. Peco Fasteners makes no claim of warranty in the accuracy of this information. Users of this information are solely responsible for protecting themselves against liability. It is solely the responsibility of the purchasers and users of these fasteners to consult with Engineers that are experts in an applicable field. Peco Fasteners is not responsible for any loss, claim, or damage due to these specification sheets.

5/30/18