



CORD SET PORTABLE GFCI, MANUAL RESET

1594CS1M | [Pass & Seymour](#)

FEATURES & BENEFITS

Portable Ground Fault Circuit Interrupter, 1' Cord Set 15amp 125volt, Manual Reset



- Durable polycarbonate case withstands hard use.
- Has bright, green power indicator light that is on when power is available.
- Open neutral protection.
- Optional Turnlok plugs and connectors prevent accidental disconnection.
- Optional tri-cord connector handles up to three loads.
- 10kA short circuit rating.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Yellow

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Standard: C22.2 No. 42, 144

cULus: Yes

cUL Standard: Yes

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121614

DIMENSIONS

Length (US): 13.6"

TECHNICAL INFORMATION

Amps: 15A

NEMA Configuration Number: 5-15P/R

NEMA Rating: Yes

Volts: 125V

Volts (AC): 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA

Buy American Act Status: No



CORD SET PORTABLE GFCI, MANUAL RESET

1594CS1M | [Pass & Seymour](#)

FEATURES & BENEFITS

Portable Ground Fault Circuit Interrupter, 1' Cord Set 15amp 125volt, Manual Reset



- Durable polycarbonate case withstands hard use.
- Has bright, green power indicator light that is on when power is available.
- Open neutral protection.
- Optional Turnlok plugs and connectors prevent accidental disconnection.
- Optional tri-cord connector handles up to three loads.
- 10kA short circuit rating.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Yellow

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Standard: C22.2 No. 42, 144

cULus: Yes

cUL Standard: Yes

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121614

DIMENSIONS

Length (US): 13.6"

TECHNICAL INFORMATION

Amps: 15A

NEMA Configuration Number: 5-15P/R

NEMA Rating: Yes

Volts: 125V

Volts (AC): 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA

Buy American Act Status: No