



## CORD SET PORTABLE GFCI, MANUAL RESET

1594CS1M | [Pass & Seymour](#)

### FEATURES & BENEFITS

Portable Ground Fault Circuit Interrupter, 1' Cord Set 15amp 125volt, Manual Reset



- Durable polycarbonate case withstands hard use.
- Has bright, green power indicator light that is on when power is available.
- Open neutral protection.
- Optional Turnlok plugs and connectors prevent accidental disconnection.
- Optional tri-cord connector handles up to three loads.
- 10kA short circuit rating.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Yellow

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Standard: C22.2 No. 42, 144  
cULus: Yes  
cUL Standard: Yes  
UL Listing No: UL498  
UL Standard: Yes  
UN SPSC: 39121614

#### DIMENSIONS

Length (US): 13.6"

## TECHNICAL INFORMATION

Amps: 15A

NEMA Configuration Number: 5-15P/R

NEMA Rating: Yes

Volts: 125V

Volts (AC): 125

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA

Buy American Act Status: No