



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2011S Copper Splice Cap Crimp Conn, 14-4 Awg, 50/Bag

Ideal

Catalog Number	2011S
Manufacturer	Ideal
Description	Splice Cap, Copper Conductor Material, 600 V Ac, 0.01 LB
Weight per unit	0.2500 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

Material	Copper Sleeves
Voltage Rating	600

Material, Color, and Finish

Finish	Zinc-Plated, Tin-Plated Steel Sleeves
--------	---------------------------------------

Descriptions

Description	COPPER SPLICE CAP CRIMP CONN, 14-4 AWG, 50/BAG
extra long description	IDEAL 2011S SPL CAP, 50PC BAG
Features	Designed for making fast, permanent, pressure-type connectionsSolid copper sleeves require less crimping pressure and resistn corrosion in harsh environmentsUL 486S Listed and CSA C22.2 #188 Certified: comply with Federal Specification W-S-61D

Manufacturer Information

Brand	Buchanan
GTIN	00781789450070
UPC	781789450070

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	Splice Cap

Availability

minimum qty	50
-------------	----

Packaging

Carton	50
Package	500
Weight Per each	0.25

Uses, Certifications, and Standards

Application	For Buchanan C24 Crimp Tool And Designed For Fast, Permanent, Pressure-Type Connections
standard	CSA, UL Listed, RoHS