

# Eaton 20206-12

Catalog Number: 20206-12

Eaton B-Line series wall mounted panel enclosure, 20" height, 6" length, 20" width, NEMA 12, Hinged cover, 12 enclosure, Wall mount, Medium single door, External mounting feet, Carbon steel, Seamless poured in-place gasket



## General specifications

Product Name	Catalog Number
Eaton B-Line series type 12 panel enclosures	20206-12
	UPC
	782051800203
Product Length/Depth	Product Height
6 in	20 in
Product Width	Product Weight
20 in	25.2 lb
Certifications	
UL 508A	
CSA C22.2.	
NEMA	

## Material/finish

### Material

Carbon steel

### Wall thickness

16 gauge

### Finish color

Painted

### Color

ANSI 61 gray

## Model

### Style

Medium single door

### Model

12 enclosure

### Cover type

Hinged

### Mounting method

Wall

### Mounting hole details

External mounting feet

### Locking provisions

Padlock provision

### Closure type

Hinged

### Special features

Plated door clamps

## Standards

### NEMA Rating

12

### Country of origin

US

## Resources

### Catalogs

[Disconnect Enclosure Catalog](#)

### Specifications and datasheets

[Eaton Specification Sheet - 20206-12](#)