



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



20T3QCLAX12V HLGN Bipin LMP

Sylvania-Ledvance

Catalog Number	20T3QCLAX12V
Manufacturer	Sylvania-Ledvance
Description	OBS58694 Tungsten Halogen Quartz Bi Pin Starlite Low Pressure Clear Finish Uv Filter With Axial Filament G4 Bi Pin Base 20WATT 12VOLT 4000HR Lamp Life
Weight per unit	0.0200 (lbs/each)
Product Category	Lighting

Features

average life	2000
Base	G4 Bipin
dimnable	Yes
lumens	320
Shape	T3
start type	Instant
Voltage Rating	12
Wattage	20

Material, Color, and Finish

color rendering index (cri)	100
color temperature	3000
Finish	Clear

Descriptions

Description	HLGN BIPIN LMP
extra long description	SYL 20T3Q/CL/AX-12V/58694 20T3QCLAX
Long Description	OBS58694 Tungsten Halogen Quartz Bi Pin STARLITE Low Pressure Clear Finish UV Filter With Axial Filament G4 Bi Pin Base 20Watt 12Volt 4000Hr Lamp Life
Product Type	20T3QCLAX 12V 40/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135586941
Manufacturers Part Number	20T3Q/CL/AX-12V/58694
sub brand	STARLITE Bi-Pin
UPC	046135586941

Taxonomies, Classifications, and Categories

Category Description	QUARTZ
Type	HALOGEN



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	40
Weight Per each	0.02

Uses, Certifications, and Standards

Application	Medium Screwbase or bi-pin
-------------	----------------------------