



*Commercial, Industrial
and Residential Electrical Products*

4 In. Square Box, Welded, 2-1/8 In. Deep, Ten 1/2 In. KO's & Six TKO's, Raised Ground

Catalog #:
232



FEATURE BENEFIT

Welded 4 In. square box for installing receptacles, switches or fixtures in walls or ceilings

PRODUCT FEATURES

- Combination screw heads allow quick installation
- Welded construction
- Eight 1/2 In. knockouts and four TKO knockouts
- 30.3 Cu. In. capacity
- Raised ground
- Acceptable in 2-hour fire rated walls

APPLICATIONS

Square box is used where multiple conductor runs are split into two or more directions to bring power to a number of electrical devices inside walls or ceilings for lighting fixtures, switches or receptacles

CERTIFICATIONS



PRODUCT SPECIFICATIONS

UPC Number:	050169902325
Ea Length/Depth (in.):	4.00
Ea Width (in.):	4.00
Ea Height (in.):	2.20
Wt. Ea. (Lbs.):	0.850
Package Type:	Loose
Product UPC-A Labeled:	No



All RACO single-gang, two-gang, 4 In. square, and single gang gangable U.L. listed steel boxes are acceptable for use in 2-hour fire rated walls. For additional information, consult U.L. "Fire Resistance Directory" or the U.L. website at www.ul.com

SHIPPING

Case 12of5:	50050169902320
Standard Carton Qty:	25
Min Order Qty:	25

600V Per UL 514-A, suitable for use without a bonding jumper in circuits up to 600 volts



**COMMERCIAL
CONSTRUCTION**
A Division of Hubbell Incorporated (Delaware)

RACO
3902 W. Sample St.
South Bend, IN 46619
574-234-7151
www.hubbell.com/raco/en

