



## 4 in. Square Box, Welded, 2-1/8 in. Deep, Ten 1/2 in KO's & Six TKO's, Raised Ground

By Raco  
Catalog # [232](#)

4 in. Square Box, Welded, 2-1/8 in. Deep, Ten 1/2 in KO's & Six TKO's, Raised Ground



### Features

- Combination screw heads allow quick installation
- Welded construction
- Ten 1/2 in KO's & Six TKO's
- UL Listed
- 30.3 cu. in. capacity
- Raised ground
- Acceptable in 2-hour fire rated walls

### General

Bracket Type	No Bracket
Drawn or Welded	Welded
EU RoHS Indicator	Yes
Fire Resistance	Yes
Knockouts	1/2 in; 1/2 - 3/4 in Combination (TKO)
Material	Steel
Type	<ul style="list-style-type: none"><li>• Box</li><li>• Box</li></ul>
UPC	050169902325
Wiring System	Conduit

### Dimensions

Actual Depth	2.434 in
Cubic Capacity	30.3 cu.in
Depth	2.125 in
Height	4 in
Raised Ground	Yes
Weight	0.898 lb
Width	4 in

### Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

### Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1750

### Product Assets

[Brochures - Product Solutions for Electrical Prefabrication](#)  
[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - LEED Statement](#)  
[Certifications - NEMA OS1](#)  
[Certifications - UL COC - E195978-5](#)  
[Sales Drawings - RACO-welded-steel-box-infographic](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-232-SPEC-EN | REV 5/2024