

Eaton 24248 RHC

Catalog Number: 24248 RHC

Eaton B-Line series Type 3/3R panel enclosures, 24" height, 8" length, 24" width, NEMA 3R, Hinged cover, RHC enclosure, Wall mount, Medium single door, External mounting feet, Carbon steel



General specifications

Product Name	Catalog Number
Eaton B-Line series Type 3/3R panel enclosures	24248 RHC
	UPC
	782051407556
Product Length/Depth	Product Height
8 in	24 in
Product Width	Product Weight
24 in	50 lb

Certifications

UL 50
CSA C22.2.
NEMA



Powering Business Worldwide

Material/finish

Material

Carbon steel

Wall thickness

14 gauge

Finish color

Painted

Color

ANSI 61 gray

Model

Style

Medium single door

Model

RHC enclosure

Cover type

Hinged

Mounting method

Wall

Mounting hole details

External mounting feet

Locking provisions

Padlock provision

Closure type

Hinged

Special features

Rain hood, plated screws, piano hinge with s.s. pin

Standards

NEMA Rating

3R

Country of origin

US

Resources

Catalogs

[Type1-3-3r-enclosure-catalog-section](#)

Specifications and datasheets

[Eaton Specification Sheet - 24248 RHC](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)