



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



253SRTI 1-1/4" Ins Steel Emt Raintight Compression Conn *Bridgeport Fittings*

Catalog Number	253SRTI
Manufacturer	Bridgeport Fittings
Description	Compression Connector, 1-1/4 In Trade Size, Straight Connection Orientation, Zinc Electro-Plated, Insulated, 2-11/16 In Length, 1-15/16 In Diameter, +105 °C Operating Temperature, 0.0168 LB/Ea
Weight per unit	0.0168 (lbs/each)
Product Category	Steel Insulated Straight Compr

Features

Connector Type	Steel Raintight/Concrete-Tight Insulated
insulation	Insulated Throat
Material	Steel
media	Yes

Material, Color, and Finish

Finish	Zinc Electroplated
--------	--------------------

Dimensions and Weight

Size	1 1/4
------	-------

Descriptions

Description	1-1/4" INS STEEL EMT RAINLIGHT COMPRESSION CONN
extra long description	BPT 253-SRTI 1-1/4" STEEL RAINLIGHT

Manufacturer Information

Brand	Bridgeport
GTIN	00781747122537
UPC	781747122537

Taxonomies, Classifications, and Categories

Category Description	STEEL EMT FITTINGS
Type	CONNECTOR

Packaging

Carton	25
Weight Per each	0.0168

Uses, Certifications, and Standards

Application	Used to join EMT to box or enclosure. Concrete tight/Raintight. Insulated Throat - 105°C. Patented
standard	cULus
Temperature Rating	105°C