



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 256SRTI 2-1/2" Ins Steel Emt Raintight Compression Conn *Bridgeport Fittings*

Catalog Number	256SRTI
Manufacturer	Bridgeport Fittings
Description	Connector, Compression, Steel, Insulated Throat - 105 Degree C, Size 2 1/2"
Weight per unit	1.6 (lbs/each)
Product Category	Steel Insulated Straight Compr

### Features

Connector Type	Steel Raintight/Concrete-Tight Insulated
insulation	Insulated Throat
Material	Steel
media	Yes

### Material, Color, and Finish

Finish	Zinc Electroplated
--------	--------------------

### Dimensions and Weight

Size	2-1/2
------	-------

### Descriptions

Description	2-1/2" INS STEEL EMT RAINLIGHT COMPRESSION CONN
extra long description	BPT 256-SRTI 2-1/2" STEEL RAINLIGHT
Features	Think Orange: Quality In, Water Out. Listed for Damp or Wet Locations.
Long Description	Connector, Compression, Steel, Insulated Throat - 105 Degree C, size 2 1/2"
Product Type	2-1/2" Steel Raintight Conn, I
Special Features	Connectors assembled with knockout gasket, no separate pieces to buy and stock

### Manufacturer Information

Brand	Bridgeport
GTIN	00781747122568
Manufacturers Part Number	256-SRTI
UPC	781747122568

### Taxonomies, Classifications, and Categories

Category Description	STEEL EMT FITTINGS
Type	CONNECTOR

### Trade Size

Trade Size	2-1/2
------------	-------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	2
Package	10
Weight Per each	1.61

## Uses, Certifications, and Standards

Application	Used to join EMT to box or enclosure. Concrete/Raintight. Insulated Throat - 105°C. Patented
standard	cULus
Temperature Rating	105°C