




GE  
Lighting

14641 - 25T61/2

GE T6.5



**GENERAL CHARACTERISTICS**

Lamp Type	Incandescent - Tubular
Bulb	T6.5
Base	Intermediate Screw (E17)
Filament	C-8
Bulb Finish	Clear
Rated Life	1000.0 hrs
Bulb Material	Soft glass

**PHOTOMETRIC CHARACTERISTICS**

Initial Lumens	244.0
Nominal Initial Lumens per Watt	9

**ELECTRICAL CHARACTERISTICS**

Wattage	25.0
Voltage	130.0
Estimated Energy Cost per Year	3.01

**DIMENSIONS**

Maximum Overall Length (MOL)	5.5000 in(139.7 mm)
Bulb Diameter (DIA)	0.813 in(20.7 mm)

**PRODUCT INFORMATION**

Product Code	14641
Description	25T61/2
Standard Package	Case
Standard Package GTIN	10043168146415
Standard Package Quantity	60
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	60
UPC	043168146418