

# Specification Grade Decorator Switch, Light Almond

2621LA



Single Pole, Back and Side Wire, Decorator Switch, 120/277 volts, Light Almond.

## features & benefits

- Impact-resistant polycarb back body and frame.
- Cushioned thermoplastic paddle assures smooth, quiet, long term operation.
- Unique single rocking butterfly contact provides long term consistent performance with significantly fewer moving parts.
- Internal screw-pressure-plate back and side wire capability for easy installation with #14 - #10 stranded or solid copper/copper clad wire.
- Terminals made of high conductivity brass and serrated for maximum wire gripping.
- Silver alloy contacts integrally formed to the butterfly actuator assures reliable performance.
- Integral auto-ground clip for positive ground to metal boxes.
- Tri-drive ground, terminal, and mounting screws.
- All terminal screws backed out, ready-to-install.



## specifications

### General Info

Number Of Poles: 1  
Style: Decorator

### Listing Agencies/Third Party Information

CSA Listing Info: C22.2 111  
CSA Standard: Yes

UL Listing No: 20  
UL Standard: Yes  
UN SPS C: 39121507

**Dimensions**

Depth U S: 1.06"  
Height U S: 3.531"  
Width U S: 1.3"

**Technical Information**

Amps: 15 Amp  
Volts: 120/277VAC  
Volts A C: 120/277

**Buy American Act Compliance**

Country of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant