



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



301066 Underground Wire Conn, 66 Gray/DK Blue, 50/Box

Ideal

Catalog Number	301066
Manufacturer	Ideal
Description	Undergrd Gray MDL 66 50 Box
Weight per unit	5.5 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

Quantity	Box of 50
----------	-----------

Material, Color, and Finish

Color	Gray
-------	------

Descriptions

Description	UNDERGROUND WIRE CONN, 66 GRAY/DK BLUE, 50/BOX
extra long description	IDEAL 30-1066 UNDERGRD GRAY MDL 66
Features	100% Silicone-based sealant protects against moisture and corrosionUL Listed to 486G Sealed Twist-On Wire Connector for use in damp/wet locations or above-grade applicationsEasy to apply, pre-filled twist-on wire connectorsExpanding, live-action square-wire spring for fast, secure and long-lasting connectionsDeep skirt provides superior moisture resistance to protect connectionsTough, UL 94V-2 flame-retardant shell rated at 105°C (221°F)For use in damp/wet location or direct burial/below-grade applications
Long Description	UNDERGRD GRAY MDL 66 50 BOX
Product Type	Undergrd Gray MDL 66 50 Box
Special Features	Silicone-based sealant protects against moisture and corrosion

Manufacturer Information

Brand	Ideal
GTIN	00783250761876
Manufacturers Part Number	30-1066
sub brand	Underground®
UPC	783250761876

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	Model 66® Wire Connector

Availability

minimum qty	50
-------------	----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	50
Weight Per each	5.48

Uses, Certifications, and Standards

Application	Handles wire sizes from #14 to #6 AWG copper. Minimum of 3 #12 AWG. Maximum of 2 #6 & 1 #10 AWG.
standard	UL Listed to 486D for use with direct burial
Temperature Rating	105