



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 30144 Twister Pro Wire Conn, 344 Red/Tan, 50/Box

*Ideal*

Catalog Number	30144
Manufacturer	Ideal
Description	Ideal, Wire Connector, Twister Pro, Conductor Range: 22 - 8 Awg, 2/18 Awg Min, 4/10 Awg Max, Number Of Conductors: 2 to 4, Material: Flame-Retardant Polypropelene, Color: Red/Tan, Voltage Rating: 600 V, Environmental Conditions: Tough, UI 94V-2 Flame-Retardant Shell Rated At 105 Deg C (221 Deg F), Wire Type: Cu/Cu, Model Number: 344
Weight per unit	0.4750 (lbs/each)
Product Category	Electrical Fixture Conn ( Nuts

### Features

Material	Flame-retardant Polypropelene
Voltage Rating	600
Wire Type	COPPER

### Material, Color, and Finish

Color	Red/Tan
-------	---------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	TWISTER PRO WIRE CONN, 344 RED/TAN, 50/BOX
extra long description	IDEAL 30-144 TWISTER PRO 344 RED TA
Features	Twister Wire Connectors have earned a solid reputation as the most technically advanced wire connector available. These superior wire connectors are designed from top to bottom with features to provide more comfort and less fatigue to professional electricians. With swept wings and an expanding, live-action spring, the Twister supports a wide range of common wiring configurations with comfort and ease, even on the toughest combinations like solid-to-stranded. The copolymer shell expands for smooth, progres
Long Description	IDEAL, Wire Connector, Twister PRO, Conductor Range: 22 - 8 AWG, 2/18 AWG Min, 4/10 AWG MAX, Number Of Conductors: 2 to 4, Material: Flame-retardant Polypropelene, Color: Red/Tan, Voltage Rating: 600 V, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 DEG F), Wire Type: Cu/Cu, Model Number: 344
Product Type	Twister Pro 344 Red Tan, 50 BX
Special Features	1,000V Maximum In Fixtures And Signs;Better Grip And More Leverage For Faster Connections With Less Effort;Comfortable Swept Wings Designed To Help Reduce Hand Fatigue;Comply With Federal Specification W-S-610E;Expanding Square-Wire Spring Provides A Secure Connection Every Time;Features: The Widest Red/Tan Wire Range In The Industry;Min. 2 #18 To Max. 4 #10;Model Number: 344;Suregrip Overmolding Provides Better Grip For Improved Leverage And More Torque;Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 D

## Manufacturer Information

Brand	Ideal
GTIN	00783250707812
Manufacturers Part Number	30-144
UPC	783250707812

## Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
----------------------	--

## Availability

minimum qty	50
-------------	----

## Packaging

Carton	50
Package	500
Weight Per each	0.475



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Insulating or Joining 1 or more conductors
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 DEG F)
standard	CSA C22.2 #188, UL 486C Listed, RoHS