



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



302GC120 Selectone 30W Amplified Speaker 120V

Federal Signal Corp.

Catalog Number	302GC120
Manufacturer	Federal Signal Corp.
Description	Selectone 30 Watt Amplified Speaker, 120VAC, Gray - Available In 24VAC/DC, 120VAC and 240VAC. Built-In Gain Control, Adjustable Between 0 DbA to 114 DbA At 10 Feet (100 DbA to 124 DbA At 1 Meter). Type 3R, IP54 Enclosure. Digital Signal Amplification. Fused Input and Output. Indoor/Outdoor Use. CSFM Approved. UL and CUL Listed.
Weight per unit	8.9 (lbs/each)
Product Category	Sound & Audio Systems

Features

dimensions	13.9 H x 10.2 W x 9.9 D
Material	Die-Cast Aluminum
Operating Current	0.30
Operating Voltage	120VAC 50-60Hz
Output Level	30

Material, Color, and Finish

Color	Gray
-------	------

Descriptions

Description	SELECTONE 30W AMPLIFIED SPEAKER 120V
extra long description	FED-SIG 302GC-120 SELECTONE 30W AMP
Long Description	SelectTone 30 Watt Amplified Speaker, 120VAC, Gray - Available in 24VAC/DC, 120VAC and 240VAC. Built-in gain control, adjustable between 0 dBa to 114 dBa at 10 feet (100 dBa to 124 dBa at 1 meter). Type 3R, IP54 enclosure. Digital signal amplification. Fused input and output. Indoor/outdoor use. CSFM Approved. UL and cUL Listed.
Product Type	Selectone 30W Amplified Speaker 120V
Special Features	Digital Signal Amplification

Manufacturer Information

Brand	Federal Signal
GTIN	00782979200802
Manufacturers Part Number	302GC-120
UPC	782979200802

Taxonomies, Classifications, and Categories

Type	Amplified Speaker
------	-------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	8.9

Uses, Certifications, and Standards

Application	Indoor/Outdoor
Enclosure	Type 3R, IP54
Mounting	SURFACE
Operating Temperature	-67 to 150
standard	UL Listed/cUL Listed/CSFM Approved