



Job Name:

Job Type:

Comments:

Quantity:

31361-829: Five-Light Rialto Chandelier



Dimensions:

Diameter: 25 1/2"

Height: 21"

Overall Height: 142"

Wire: 144" (color/Brown)

Chain: 120"

Mounting Proc.: Center Lock-Up

Connection: Mounted To Box

Bulbs:

- 5 - Medium A19 100w Max. 120v - Not included
- 5 - LED Medium A19 8w Max. 120v - Not included
- 5 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Easily converts to LED with optional replacement lamps
- Supplied with wire pre-laced through chain

Material List:

- 1 Body - Steel - Russet Bronze
- 1 Arms - Steel - Russet Bronze
- 1 Chain - Steel - Russet Bronze

Safety Listing:

- UL Listed for Dry Locations
- cUL Listed for Dry Locations

Instruction Sheets:

- English (HC-706)
- French (F-004)

Collection: Rialto

Five Light Decorative Chandelier in Russet Bronze Finish with Ginger Glass Shades

Five-light chandelier in a Russet Bronze finish with Ginger glass.

UPC #:785652361821

Finish: Russet Bronze (829)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Ginger	5					6 1/2				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy			1 5/16	6		

Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	31361-829	1	785652361821	17	16	20.25	3.188	20.24	125	Yes
NJ Pallet		24		48	40	72	80	485.76		No

NV Pallet		24		48	40	72	80	485.76		No
-----------	--	----	--	----	----	----	----	--------	--	----