# TradeMaster Tamper-Resistant Receptacle

3232TR

Tramper-Resistant Duplex
Grounding Receptacle. 15 amp, 125 volt.
Brown.



# features & benefits

- Meets 2008 National Electrical Code Tamper-Resistant requirements.
- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- High-impact resistant thermoplastic construction.
- Extra-long strap.
- Quickloop wire looping aid.
- Long-term blade retention.
- Longer tri-drive screws for easier 12 AWG looping.
- Extra-large circuit break-off tabs.
- Side-access push wire release.
- Ultrasonic welding of face to back body.
- Side wire accepts #12 #14 AWG solid wire.
- Push wire accepts #14 AWG solid only.
- Superior protection than traditional outlet caps or protection plates.
- Low profile face.
- Traditional contoured face (3232 models).
- Self-grounding models provide automatic ground clip.

specifications

#### **General Info**

Color: Brown

Type: Tamper-Resistant

## **Listing Agencies/Third Party Information**

CSA Listing Info: C22.2 No.42

CSA Standard: Yes

cULus: Yes Federal Spec: No UL Listing No: UL498 UL Standard: Yes

UN SPS C: 39121406

#### **Dimensions**

Depth U S: 1" Height U S: 3.31" Width U S: 1.32"

### **Technical Information**

Amps: 15 Amp Volts A C: 125

### **Buy American Act Compliance**

Country of Origin: CHINA Buy American Act Status: No