



Job Name:

Job Type:

Comments:

Quantity:

41145-814: Single-Light Acadia Wall Light



Dimensions:

Width: 7" **Extends:** 8 1/4"
Height: 11 1/4" **Wire:** 6 1/2"

Mounting Proc.: Cap Nuts
Connection: Mounted To Box

Bulbs:

- 1 - Medium A19 100w Max. 120v - Not included
- 1 - LED Medium A19 8w Max. 120v - Not included
- 1 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Easily converts to LED with optional replacement lamps
- Fixture may be mounted in the up or down position

Material List:

1 Body - Steel - Misted Bronze

Safety Listing:

UL Listed for Damp Locations
cUL Listed for Damp Locations

Instruction Sheets:

English (HC-1007)
French (F-007)

Collection: Acadia

Decorative One Light Wall Sconce In Misted Bronze Finish with Champagne Seeded Glass Shade

European Rustic combines comfort and sophistication. The Misted Bronze is a mix of dark & russet browns that suggests warmth. The Champagne Seeded glass creates soft romantic glows.

UPC #:785652411458

Finish: Misted Bronze (814)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Champagne Seeded	1					5 1/16				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate			1 3/4	6	5 1/2	5 3/4

Replacement Bulb Data:

Product #	Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted	A19	8	8	120v	50000	450	3000	85
97408S	Frosted	A19	8	8	120v	50000	450	2700	85
97309S	Frosted	A19	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted	A19	13.5	13.5	120v	50000	800	2700	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	41145-814	1	785652411458	9.75	7	13.5	0.533	3.45	125	Yes

NJ Pallet		120		48	40	74	82.222	414		No
NV Pallet		120		48	40	74	82.222	414		No