

Eaton 4412 G NK

Catalog Number: 4412 G NK

Eaton B-Line series wireway, 4" height, 12" length, 4" width, G NK wireway, Thru holes, No knockouts, Screw cover, NEMA 1, Steel, Plated screws, ANSI 61 gray, 16 gauge

General specifications



Product Name	Catalog Number
Eaton B-Line series wireway	4412 G NK
UPC	Product Length/Depth
782051440164	12 in
Product Height	Product Width
4 in	4 in
Product Weight	Certifications
3.309 lb	CSA Certified
	UL Listed

Material/finish

Material thickness

16 gauge

Finish color

ANSI 61 gray

Model

Closure type

Plated screws

Mounting method

Thru holes

Special features

Cover is secured to the body with plated screws

Type

G NK wireway

Resources

Catalogs

[EnviroShield Wireway Flyer](#)

Specifications and datasheets

[Eaton Specification Sheet - 4412 G NK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)