



Product Number: 12420

Order Abbreviation: 60A/RS/2/RP 130V

General Description: Incandescent A19 Bulb Shape Rough Service Inside Frost Finish Medium Aluminum Base 60Watt 130Volt Retail Pack 24Bulbs Per Case 2Bulbs Per Package

*** Full Case Required**

Product Information

Abbrev. With Packaging Info.	60ARS2RP 130V 24/CS 2/SKU
Approx. Lumens	555
Average Rated Life (hr)	1000
Base	Medium
Bulb	A19
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2850
Diameter (in)	2.375
Diameter (mm)	60.33
Family Brand Name	ROUGH SERVICE
Filament	C-9
Lamp Finish	Inside Frost
Light Center Length - LCL (in)	2.875
Light Center Length - LCL (mm)	73
Maximum Overall Length - MOL (in)	4.438
Maximum Overall Length - MOL (mm)	112.7125
Nominal Voltage (V)	130.00
Nominal Wattage (W)	60.00



ECOLOGIC
TM



Footnotes

- Incandescent lamps operated at less than rated voltage provide a lower light output, longer life, lower color temperature and are less efficient in terms of lumens per watt.
- @ 120 volts, approximate 53 watts, 420 lumens, 2500 hours



Product Number:

12420

Order Abbreviation:

60A/RS/2/RP 130V

General Description: Incandescent A19 Bulb Shape Rough Service Inside Frost Finish Medium Aluminum Base 60Watt 130Volt Retail Pack 24Bulbs Per Case 2Bulbs Per Package

*** Full Case Required**

Product Information

Abbrev. With Packaging Info.	60ARS2RP 130V 24/CS 2/SKU
Approx. Lumens	555
Average Rated Life (hr)	1000
Base	Medium
Bulb	A19
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2850
Diameter (in)	2.375
Diameter (mm)	60.33
Family Brand Name	ROUGH SERVICE
Filament	C-9
Lamp Finish	Inside Frost
Light Center Length - LCL (in)	2.875
Light Center Length - LCL (mm)	73
Maximum Overall Length - MOL (in)	4.438
Maximum Overall Length - MOL (mm)	112.7125
Nominal Voltage (V)	130.00
Nominal Wattage (W)	60.00



ECOLOGIC
TM



Footnotes

- Incandescent lamps operated at less than rated voltage provide a lower light output, longer life, lower color temperature and are less efficient in terms of lumens per watt.
- @ 120 volts, approximate 53 watts, 420 lumens, 2500 hours