

I/R Stylus® Alkaline Battery-Powered Pen Light

Case Material: Water-proof, machined aluminum case with anodized finish and non-slip, knurled grip comes in olive drab green

Dimensions: Length: 6.21 in. (15.17 cm) Diameter: 0.375 in. (0.95 cm)

Weight: 1.1 oz (31.19 grams)*

Light Source: High-intensity “solid-state” 100,000 hour IR LED

On/Off: Features a momentary blink switch and constant “on”

Run Time: Up to 60 hours.

Battery: 3 “AAAA” size alkaline batteries.

- Features:**
- Waterproof
 - 880nm IR LED
 - Pocket clip
 - Sharp Spot, Glare Guard Protector (Included)
 - Compatible with most night vision goggles



Approvals:** Most models meet applicable European Community Directives

Warranty: Limited lifetime warranty.

*With battery (included in purchase).

**See product for specific ratings.



Item	UPC	Part #
Stylus Accessory Pack OD Green I/R LED	080926-65089-3	65089
Glare Guard	080926-65031-2	65031
Lanyard with Push Button Slide	080926-72024-4	72024
AAAA Batteries – 6 pack	080926-65030-5	65030

