

Project Name

Location

Prepared By



NUVO 65-718

LED 2 BULLET HEAD SECURITY LGT

Notes

(revised) 10-27-2023 05:20:07

General

Status	Active
Fixture Type	Security Lighting
Finish	Bronze
Wattage	20W
Lumen Output	1900L
CCT (Kelvin)	4000K
Temperature	Cool White
IP Rating	IP65
Indoor or Outdoor Fixture	Outdoor

Specifications

Technology	LED
CRI	80+
Voltage	120V-277V
Beam Angle	50
Rated Hours	50000
Operating Temperature	-30C (-22F) to +50C (+122F)
Dimmable	Non-Dimmable
Photocell or Sensor	No Photocell
Lens Material	Glass
Surge Protection	Built-in surge protection - 2KV
Weight (lb.)	2.41
Material	Die-Cast Aluminum

Dimensions

Height (in.)	4.54
Width (in.)	8.16
Extension (in.)	8.8

Compliance

Safety Listing	cETLus - Listed
Location Rating	Wet
ENERGY STAR	No
DLC Approved	No
ADA Compliant	No
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
Canadian Standard ICES-005	Class A
SDS Sheet	LED_Fixture

Additional Information

Specification Note	Adjustable Angle from 0 to 90 degrees
Warranty	5-Years