


TradeMaster Grounding Toggle Switch

660G



*Available in bulk packs of 120. Add "U" to end of Catalog Number. Example: 660GU



features & benefits

- Side wire #12 and #14 AWG. Push wire #14 AWG.
- Tri-drive ground, terminal, and mounting screws.
- Easy-access green hex head ground screw.

specifications

General Info

Product Series: TradeMaster

Type: Toggle Number Of Poles: 1

Special Features: Self-Grounding

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 111

CSA Standard: Yes UL Listing No: 20 UL Standard: Yes UN SPS C: 39121406

Dimensions

Depth U S: 1.090" Height U S: 3.281" Width U S: 1.25"

Technical Information

Amps: 15 Amp Volts: 120VAC Volts A C: 120

Buy American Act Compliance

Country of Origin: CHINA

Buy American Act Status: Trade Agreement Act Compliant