

# Eaton 6624 HS

Catalog Number: 6624 HS

Eaton B-Line series wireway, 6" height, 24" length, 6" width, HS wireway, Thru holes, 7 top knockouts, 7 bottom knockouts, Hinged cover, NEMA 1, Steel, Hinged, ANSI 61 gray, 16 gauge

## General specifications



|                             |                             |
|-----------------------------|-----------------------------|
| <b>Product Name</b>         | <b>Catalog Number</b>       |
| Eaton B-Line series wireway | 6624 HS                     |
| <b>UPC</b>                  | <b>Product Length/Depth</b> |
| 782051478037                | 24 in                       |
| <b>Product Height</b>       | <b>Product Width</b>        |
| 6 in                        | 6 in                        |
| <b>Product Weight</b>       | <b>Certifications</b>       |
| 9.951 lb                    | CSA C22.2.<br>UL Listed     |

## Material/finish

### Material thickness

16 gauge

### Finish color

ANSI 61 gray

## Model

### Closure type

Hinged

### Mounting method

Thru holes

### Special features

Cover is secured to the body with plated screws

### Type

HS wireway

## Resources

### Catalogs

[EnviroShield Wireway Flyer](#)

### Specifications and datasheets

[Eaton Specification Sheet - 6624 HS](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)