

# TradeMaster Grounding Toggle Switch, Black

663BKG



Triple Pole, Grounded Terminals, 15 amps,  
120 volts, Black.

## features & benefits

- Side wire #12 and #14 AWG. Push wire #14 AWG.
- Tri-drive ground, terminal, and mounting screws.
- Easy-access green hex head ground screw.



## specifications

### General Info

Product Series: TradeMaster  
Type: Toggle  
Number Of Poles: 3-way  
Special Features: Self-Grounding

### Listing Agencies/Third Party Information

CSA Listing Info: C22.2 111  
CSA Standard: Yes  
UL Listing No: 20  
UL Standard: Yes  
UN SPS C: 39121406

### Dimensions

Depth U S: 1.090"  
Height U S: 3.281"  
Width U S: 1.25"

**Technical Information**

Amps: 15 Amp  
Volts: 120VAC  
Volts A C: 120

**Buy American Act Compliance**

Country of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant