

TradeMaster Grounding Toggle Switch, Brown

663G



Triple Pole Switch, Grounded Terminals, 15
amps, 120 volts, Brown.

**Available in bulk packs of 90. Add "U"
end of catalog number. Example: 663GU

features & benefits

- Side wire #12 and #14 AWG. Push wire #14 AWG.
- Tri-drive ground, terminal, and mounting screws.
- Easy-access green hex head ground screw.



specifications

General Info

Product Series: TradeMaster
Type: Toggle
Number Of Poles: 3-way
Special Features: Self-Grounding

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 111
CSA Standard: Yes
UL Listing No: 20
UL Standard: Yes
UN SPS C: 39121406

Dimensions

Depth U S: 1.090"
Height U S: 3.281"
Width U S: 1.25"

Technical Information

Amps: 15 Amp
Volts: 120VAC
Volts A C: 120

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant