



Core & Coil (71A) MH ~LT~ 175W

CORE & COIL HID MH BAL 100W M90/140 480V/120T C&C

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data

General Information					
ANSI Code	M90-M140				
Lamp Type	100 MH				
Number of Lamps	1 piece/unit				
Circuit Type	HX-HPF				
Ballast Type	Magnetic HID				
Base Model	71A5340T				
Core Size	3 X 4 (2 coil)				
Suitable For Outdoor Use	Yes				
Ignitor Catalog Number	LI533-H4				
Ignitor Temperature Rating	105°C				
Capacitor Value	10 MFD				
Capacitor Catalog Number	7C100M30RA				
Capacitor Requirements	300V				
Capacitor Temperature Rating	105°C				
Capacitor Diameter/Oval Dimensions	1.65 in				
Capacitor Height	2.75 in				
Automatic Restart	No				

Operating and Electrical				
Input Voltage	480 V			
Input Frequency	60 Hz			
Input Current (Open Circuit)	0.55 A			
Input Current (Starting)	0.3 A			
Input Current (Short Circuit)	0.24-0.36 A			
Secondary Short Circuit Current	1.35-1.65 A			
Constant Wattage Deviation	12%			
Ballast Factor (Nom)	1			
Power Factor (Nom)	0.90			
Open Circuit Voltage	260 V			
Input Current (Nom)	0.3 A A			
Input Power (Nom)	132 W			
Rated Lamp Power	100 W			
Wiring				
Wire Striplength	0.5 mm			
Wire Length by Color	12"			
Wire Type	Stranded			
Remote Wiring Configuration Allowed	Yes			


Datasheet, 2019, March 22 data subject to change

Core & Coil (71A) MH ~LT~ 175W

Max Ballast-Lamp Distance Remote Wiring 25'				
Recommended Fuse Value	2 A			
Approval and Application				
Open Circuit Voltage Test (Volts)	234-286 V			
Approval Marks	RoHS Compliant CSA certificate			
Temperature Marking	С			
UL Recognized	Yes			
Hipot Test (1 Minute)	2000 V			
Hipot Test (2 Seconds)	2500 V			
UL Insulation Class	H(180°C)			
UL Temperature Code	1029C			

Product Data	
Order product name	CORE & COIL HID MH BAL 100W M90/140
	480V/120T C&C
EAN/UPC - Product	781087094099
Order code	913700532809
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	913700532809
Net Weight (Piece)	2.627 kg

Dimensional drawing



MH BAL 100W M90/140 480V/120T C&C

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID MH BAL 100W	2.9 in	1.7 in	3.9 in	3.5 in	2.8 in	2.4 in
M90/140 480V/120T C&C						

